



KLEENGUARD* G10 POWDER-FREE GREY NITRILE GLOVES PRODUCT SPECIFICATION

<u>SIZE/CODE:</u>	<u>X-Small</u>	<u>Small</u>	<u>Medium</u>	<u>Large</u>	<u>X-Large</u>
	97820	97821	97822	97823	97824

REQUIREMENTS:

1. Style

- Grey Nitrile
- Powder Free
- Non-Sterile
- Beaded Cuff
- Textured Fingertips
- Ambidextrous

2. Barrier

- Freedom from holes (e.g. pinholes) at AQL¹ 4.0

3. Strength

<u>Before Aging</u>		<u>After Aging</u>	
<u>Tensile Strength</u>	<u>Ultimate Elongation</u>	<u>Tensile Strength</u>	<u>Ultimate Elongation</u>
<u>(MPa)</u>	<u>(%)</u>	<u>(MPa)</u>	<u>(%)</u>
28 min.	500 min.	22 min.	450 min.

As measured by ASTM D412, Standard Test Methods for Vulcanized Rubber and Thermoplastic Elastomers – Tension.
Aged according to ASTM D573, Standard Test Method for Rubber – Deterioration in an Air Oven.

4. Dimensions

- Dimensional characteristics at AQL¹ 10.0. Palm widths +/-10.

<u>Palm Width (mm) – nominal values</u>					<u>Thickness (mm)</u>		<u>Length (mm)</u>
<u>X-Small</u>	<u>Small</u>	<u>Medium</u>	<u>Large</u>	<u>X-Large</u>	<u>Palm</u>	<u>Finger</u>	<u>Cuff</u>
70	80	95	110	120	0.09 min	0.08 min	0.06 min
							240 min

As measured by ASTM D6319, Standard Practice for Nitrile – Measurement of Dimensions

5. Packaging

- 100 gloves (90 for XL) per dispenser box.
- 10 dispenser boxes per case.
- Shipping case and inner packaging labeled with product name, size, lot/batch and catalogue number

1. AQL levels defined according to ISO 2859-1 for sampling by attributes.

Additional Information:

For additional information, contact your local Kimberly-Clark representative or email
Tech_Asia@kcc.com